



EOP max² Heat Exchanger

The natural evolution of the winning EOP design

MAIN FEATURES

- ◆ Multiple gasketed disks rotor
- ◆ Presettable speed with inverter controlled acceleration
- ◆ Lowest pressure loss on primary circuit due to pumping action
- ◆ Gravity fed
- ◆ Low pressure loss on secondary circuit rotor fully electropolished
- ◆ High rotational speed

BENEFITS

- ◆ High efficiency tuned at 65-75%
- ◆ Extremely low fouling
- ◆ Low maintenance
- ◆ Higher flexibility due to the possibility to replace single disks
- ◆ More robust